



# iLOQ Armer til skåplås



A-mål (i mm)	Arm	Antall skims	B-mål (i mm)	
3	A10.16	3	Min 39,0	
4	A10.16	2	Min 39,0	
5	A10.16	1	Min 39,0	
6	A10.16	0	Min 39,0	
11	A10.14	3	Min 37,5	
12	A10.14	2	Min 37,5	
13	A10.14	1	Min 37,5	
14	A10.14	0	Min 37,5	
20	A10.96	3	Min 33,0	
21	A10.96	2	Min 33,0	
22	A10.96	1	Min 33,0	
23	A10.96	0	Min 33,0	
22	A10.68	3	Min 37,0	
23	A10.68	2	Min 37,0	
24	A10.68	1	Min 37,0	
25	A10.68	0	Min 37,0	
23	A10.69	3	Min 32,5	
24	A10.69	2	Min 32,5	
25	A10.69	1	Min 32,5	
26	A10.69	0	Min 32,5	
28	A10.99	3	Min 31,0	
29	A10.99	2	Min 31,0	
30	A10.99	1	Min 31,0	
31	A10.99	0	Min 31,0	
30	A10.17	3	Min 44,5	
31	A10.17	2	Min 44,5	
32	A10.17	1	Min 44,5	
33	A10.17	0	Min 44,5	
41	A10.13	3	Min 33,5	
42	A10.13	2	Min 33,5	
43	A10.13	1	Min 33,5	
44	A10.13	0	Min 33,5	



